

PEVQ™ — Perceptual Evaluation of Video Quality

PEVQ provides MOS estimates of the video quality degradation occurring through a network by analyzing the degraded video signal output from the network. This approach is based on modelling the behavior of the human visual tract and detecting abnormalities in the video signal quantified by a variety of KPIs.

OPTICOM, the leading provider of signal based perceptual measurement technology for voice, audio and video, offers its new easy to use real-time **PEVQ V 1.0** measurement as an OEM solution. PEVQ evaluates the quality of CIF and QCIF video formats based on perceptual measurement, reliably, objectively and fast.

PEVQ is partially based on the earlier PVQM technology developed by KPN Research and new development of OPTICOM.

Video Quality Testing

OPTICOM Product Line:

Voice/Audio Quality

PSQM ITU-T P.861

PESQ ITU-T P.862

3SQM ITU-T P.563

ECHO

PEAQ ITU-T BS.1387

Video Quality


PEVQ

Network Quality

VQmon

Principle

PEVQ is a full reference, intrusive measurement algorithm for video quality. Its basic structure is shown in the figure below.



Key Features:

- Intrusively analyzes degradation in video signals
- Outputs MOS score that correlates well with subjective MOS
- Additional KPIs for detailed analysis
- Real-time measurement with QCIF, CIF video sizes
- Perceptually based end-to-end quality analysis
- Available as DLL/Library or Source

The algorithm can be divided up into four separate blocks. The first block – pre-processing stage – is responsible for the spatial and temporal alignment of the reference and the impaired signal. This process makes sure, that only those frames are compared to each other that also correspond to each other.

The second block calculates the perceptual difference of the aligned signals. Perceptual means that only those differences are taken into account which are actually perceived by a human viewer. Furthermore the activity of the motion in the reference signal provides another

indicator representing the temporal information. This indicator is important as it takes into account that in frame series with low activity the perception of details is much higher than in frame series with quick motion.

The third block in the figure classifies the previously calculated indicators and detects certain types of distortions.

Finally, in the fourth block all the appropriate indicators according to the detected distortions are aggregated, forming the final result - the mean opinion score (MOS). The MOS value

describes the video quality on a range from 1 for very bad quality, to 5 for excellent quality. Besides the final quality score additional indicators are provided at the output of the algorithm for further cause analysis.

This approach to video quality estimation includes the effects of both packet level impairments (loss, jitter) and signal related impairments such as noise, clipping and distortions caused by coding processes. Due to the in-depth required processing, PEVQ requires considerably more processing power than e.g. VQmon. However, PEVQ and VQmon are quite complementary.

Future releases will be further optimized in computational performance and prediction accuracy as well as there will be further KPIs like Blockiness, Jerkiness, Blurriness, etc. to provide the complete picture of the quality estimate. OPTICOM's roadmap for PEVQ targets at candidating in the competition of the Video Quality Experts Group (VQEG) for the best video quality measurement model.



About OPTICOM

With PSQM, PESQ and PEAQ, OPTICOM GmbH, the pioneer in perceptual quality testing has been providing three international world-class standards for voice and audio quality measurement since its foundation in 1995. With their new single-sided speech quality measure 3SQM™, a joint development with partners, the perceptual experts from Germany now presented their fourth ITU standard. At its 10th anniversary, the presentation of the new PEVQ™ video measure leverages the company's huge experience towards the multimedia testing domain. Recognized an industry reference, OPTICOM's OPERA voice/audio quality test tools are available to users world wide. And while specialized on OEM customers in particular, the directory of OEM licensees today reads like the 'Who-is-Who' of the Telecoms industry. OPTICOM is a privately held company located in Erlangen, Germany.

Specifications

PEVQ - Perceptual Evaluation of Video Quality

Functionality

- Perceptual Evaluation of Video Quality- PEVQ, with mapping to MOS scale (1 bad, ... 5 excellent quality)

Input data

- AVI with RGB24 video data
- QCIF and CIF frame sizes
- 6 to 20 seconds in length

Output

PEVQ MOS / DMOS value

The PEVQ MOS value lies within a range from 1 (bad) to 5 (excellent). The PEVQ MOS is based on a multitude of perceptually motivated parameters. The DMOS (difference-MOS) is directly derived from the PEVQ MOS and translated into a difference scale (0=best, 4=worst).

Distortion indicators

For a more detailed analysis the perceptual level of distortion in the luminance, chrominance and temporal domain are provided.

Delay

The delay of each frame of the test signal related to the reference signal.

Brightness

The brightness of the reference and degraded signal.

Contrast

The contrast of the distorted and the reference sequence.

PSNR

To allow for a coarse analysis of the distortions in different domains the PSNR is provided for the Y, Cb and Cr components separately.

Complexity

- V1.0 is widely optimized and is capable of processing QCIF streams faster than real-time on a 3GHz Pentium 4 machine.

Platforms

- Windows
(others on request)

Sales Contacts:

OPTICOM GmbH

Nägelsbachstraße 38
91052 Erlangen, GERMANY
Phone: +49-91 31 / 530 20 - 0
Fax: +49-91 31 / 530 20 - 20
info@opticom.de
www.opticom.de

North America:

Telchemy Inc.

Phone +1-770-614-6944

Acterna U.S.

Phone +1-301 353 1560 2850

**Europe, Latin America,
Middle East & Africa,
Asia Pacific, CIS Countries:**

Acterna Germany

Phone: +49-7121 86 2222

Through our distributor network, we are represented in more than 80 countries. To find your local sales office, please contact info@opticom.de